



MEDIA ADVISORY

October 21, 2019

Excelitas Featuring Advanced Sensor and Laser Solutions at IEEE Sensors 2019

WHO: [Excelitas Technologies®](#), a global technology leader delivering innovative, customized photonic solutions, will feature its latest sensor and laser innovations at [IEEE Sensors 2019](#) in Montreal, Canada, October 28-30.

WHAT: Featured products at Excelitas' exhibit, in Booth 8, include:

- Excelitas' [C30737 Series APDs](#) are suited for LiDAR, laser meter, laser range finding and area scanning applications, providing high responsivity from 500 – 1000 nm as well as extremely fast rise times at all wavelengths, with a cut-off frequency >1 GHz for bandwidth-optimised versions. Additional applications include surveillance and automatic door opening, optical communication, 3D laser scanning and gesture recognition.
- [High volume 905nm pulsed lasers](#) – Excelitas' SMT packaged pulsed semiconductor lasers produce very high peak optical pulses centered at a wavelength of 905 nm. The package design enables light emission parallel or perpendicular to the mounting plane. These laser diodes are mounted on an FR4 substrate leadless laminate carrier (LLC) with excellent thermal management, intended for both surface mount applications and hybrid integration. Applications include LiDAR, range finding, safety light curtains, adaptive cruise control and laser therapy.
- [PGEW Series of single- and multi-epi 905nm pulsed semiconductor lasers](#) consist of a series of devices with up to four active lasing layers epitaxially grown on a single GaAs substrate chip. This multi-layer design multiplies the output power by the number of epi-layers. Applications include laser range finding, laser-based speed enforcement and IR illumination, and laser skin therapy.

WHEN: October 28 - 30, 2019

WHERE: [Palais des Congres de Montreal](#)
Montreal, Canada
Booth #8

###

About Excelitas Technologies

Excelitas Technologies® Corp. is a global technology leader focused on delivering innovative, high-performance, market-driven photonic solutions to meet the lighting, optronics, detection and optical technology needs of global customers. Serving a vast array of applications across biomedical, scientific, safety, security, consumer products, semiconductor, industrial



manufacturing, defense and aerospace sectors, Excelitas Technologies stands committed to enabling our customers' success in their end-markets. Excelitas Technologies now has approximately 6,700 employees in North America, Europe and Asia, serving customers across the world. Connect with Excelitas on [Facebook](#), [LinkedIn](#) and [Twitter](#).

Visit <http://www.excelitas.com> for more information.

Excelitas® is a registered trademark of Excelitas Technologies Corp. All other products and services are either trademarks or registered trademarks of their respective owners.

Contacts:

Scott Orr
Senior Director of Global Marketing - Commercial
scott.orr@excelitas.com
(+1) 781-996-5925

Cheryl Reynhout or Jill Anderson
On Behalf of Excelitas Technologies Corp.
SVM Public Relations
excelitas@svmmarcom.com
(+1) 401-490-9700